## QuickTap™

## **Telephone Handset Tap**



FEATURES	QT	T1	<b>T2</b>	VP
» Works with Analog, Digital, PBX, or VoIP Telephones	•	•	•	•
» 1/8" (3.5mm) Mono Audio Input				•
» 1/8" (3.5mm) Mono Audio Output	•			•
» RCA Input & Output		•	•	
» XLR Input & Output			•	
» Input Level Control			•	
» Output Level Control		•	•	•
» Switch Selects Between Carbon, Dynamic or Electret Handset Types			•	•
» Passive Design. No Battery or AC Required	•	•	•	•

THAT-1, THAT-2, and Voice Path are shown for comparison:

QT = QuickTap

T1 = THAT-1


T2 = THAT-2

VP = Voice Path

**Quick and Simple.** Connect QuickTap between your telephone and handset for quick access to audio from any telephone.

**Record Simple Interviews.** Simply unplug the handset coily cord from the base of your telephone and plug it directly into the QuickTap. Then, using the supplied cable, connect the QuickTap to the base of the telephone. Now connect your audio equipment or powered speaker to the audio output jack. This jack contains a nice mix of both sides of the conversation, as well as the tones being pressed on the keypad.

The QuickTap does not work with cellular telephones or any telephone with a keypad in the handset.



## **SPECIFICATIONS**

CE

Line	Output

1/8" (3.5mm) Mono:	600 ohms 100 mV RMS (-16 dBu nom)
Phone Line:	RJ11C
Handset Type:	Electret
Size:	2" x 2" x 1.3" (5.1 x 5.1 x 3.3 cm)
Weight:	3.4 oz

